# KINCROME TRADECENTRE

# MOBILE BENCH 13 Drawer 1600mm

Twin Lid

K7371

### OPERATION MANUAL



## IMPORTANT:

This operating manual contains important safety information, read carefully & understand all information before operating the mobile bench. Save this manual for future use.

















PARTS LIST



#### MEASUREMENTS: **WEIGHT:** 198 KG WIDTH 1600 mm DEPTH 635 mm HEIGHT 1000mm LEFT TOP DRAWER: WIDTH 833 mm DEPTH HEIGHT LEFT SMALL DRAWER: WIDTH 833 mm DEPTH 561 mm HEIGHT 78 mm LEFT LARGE DRAWER: WIDTH 833 mm DEPTH 561 mm HEIGHT RIGHT SMALL DRAWER: WIDTH 590 mm DEPTH HEIGHT 78 mm RIGHT LARGE DRAWER: WIDTH 590 mm DEPTH HEIGHT TOP TRAY x2: WIDTH 719 mm DEPTH 530 mm HEIGHT

**BENCH RATING: 25KG (PER BENCH) DRAWER RATING: 25KG (PER DRAWER) CASTOR RATING:** 1000KG [6 PIECES]

NOTE: Castors are pre fitted

## INCLUDED:



Keys x 2



Trolley Handle x 1



4 x Hex 6mm Bolts for Trolley Handle




12mm x 25 Bolts (24) for Castors



Non-Locking Castors (2)



Locking Castors (4)



15 x EVA Liners

TOOLS & ASSISTANCE REQUIRED FOR TROLLEY: "



People



For Castors: 12mm Spanner



# KINCROMEC TRADECENTRE

# MOBILE BENCH 13 Drawer 1600mm K7371

Twin Lid

### ASSEMBLY INSTRUCTIONS




**CAUTION:** Two people are recommended for

#### Step 1: Attaching the Cabinet Handle

- Position the cabinet handle (B) over the holes on the cabinet (A).
- · Attach with the bolts (AA) and tighten with supplied



NOTE: The Holes in the cabinet are tapped and do not require nuts




#### Step 2: Attaching the bottle opener

- Position the bottle opener (D) over the holes of the cabinet (A)
- . Attach with the bolts (AA) and tighten with supplied hex key(BB).




CAUTION: Do not over tighten the bolts.



#### Step 3: Attaching the storage hook

- . Position the hook (C) over the holes of the cabinet (A)
- . Attach with the bolts (AA) and tighten with supplied hex key(BB).




### MAINTENANCE

- Periodically tighten all hardware
- Periodically lubricate castors
- Lubricate the slides twice a year
- Lubricate the lock with graphite annually
- Use a damp Microfibre cloth to clean all surfaces
- Use stainless steel cleaner, to clean stainless steel surfaces

# KINCROMEC TRADECENTRE

# MOBILE BENCH 13 Drawer 1600mm K7371

TECHNICAL SPECIFICATIONS



LEFT TOP DRAWER:							
WIDTH	833 mm	DEPTH	561 mm	HEIGHT	120 mm		
LEFT SMALL DRAWER:							
WIDTH	833 mm	DEPTH	561 mm	HEIGHT	78 mm		
LEFT LARGE DRAWER:							
WIDTH	833 mm	DEPTH	561 mm	HEIGHT	136 mm		
RIGHT SMALL DRAWER:							
WIDTH	590 mm	DEPTH	561 mm	HEIGHT	78 mm		
RIGHT LARGE DRAWER:							
WIDTH	590 mm	DEPTH	561 mm	HEIGHT	136 mm		
TOP TRAY X2:							
WIDTH	719 mm	DEPTH	530 mm	HEIGHT	101 mm		

# KINCROMEC TRADECENTRE

## Twin Lid MOBILE BENCH 13 Drawer 1600mm K7371

PARTS LIST



## SPARE PARTS

ITEM	PART NO.	DESCRIPTION	QUANTITY
1	K7371-1	Lock & Key	2
2	K7371-2	Key Only (Specify Number)	2
3	K7371-13	Ball Bearing Slide Pair (Deep)	13
4	K7371-3	Stainless Steel Top	2
5	K7371-4	Trolley Handle + Bolts	1
6	K7371-5	Power Board Cover + Bolts	1
7	K7371-6	Power Board	1

ITEM	PART NO.	DESCRIPTION	QUANTITY
8	K7371-7	Power Lead Hook	2
9	K7371-8	Bottle Opener	1
10	K7371-9	Gas Struts (Pair)	2
11	K7371-10	Castor Pack (6)	1
12	K7371-11	Castor Bolt & Washer Pack	1
13	K7371-12	EVA Liner Pack	15
14	K7366-11	Trade Centre Badge	1
15	K7399	T/Centre Matched Key Pack (10)	1

#### National Head Office

National Distribution and Showroom 3 Lakeview Dve, Caribbean Business Park Scoresby Victoria 3179 Australia

ABN 41 007 185 006

Administration

T (03) 9730 7100 F (03) 9730 7199

E enquiries@kincrome.com.au W kincrome.com.au

Customer Service Centre

T 1300 657 528 F 1300 556 005



Made to Kincrome Tools & Equipment Pty Ltd global specifications and quality standards in China